

11-4143

Lamp, ACQUITY® PDA/TUV 2489/2998
Performance Maintenance Kit (2000 hr)
Comparable to: Waters® 201000281, Old # 201000186



Technical Data Sheet

1.0 Description

This lamp is designed to be compatible with Waters ACQUITY®, ACQUITY UPLC® PDA, ACQUITY® eLambda PDA, ACQUITY UPLC® TUV, 2489 Dual Wavelength UV and 2998 PDA UHPLC detectors. It is comparable to Waters® part number 201000281 and replaces old part number 201000186.



2.0 Specifications

2.1 Operating Specifications

Aperture Diameter: 0.5mm

Lifetime: 2000 hours

2.2 Materials

Socket Contacts: Pre-Tinned Brass

Connector Plug: Nylon, Natural Color

Lamp Envelope: UV Glass

3.0 Replacement Frequency

Sciencix recommends replacing the lamp when it fails to ignite repeatedly, when the detector fails to calibrate, or when noise and drift exceed application limits.

4.0 Installation Information

Sciencix parts are designed to be compatible and interchangeable with OEM parts. Please see instrument service manual for proper removal and installation procedure.

5.0 Warranty

We view your business with us as a partnership based on mutual trust.

We extend a Lifetime Warranty against any manufacturing defects on all Sciencix HPLC repair parts. If a defect is identified, please contact us at 800.682.6480 or by email at sales@sciencix.com to report the issue. We will assist you with a resolution in a timely fashion.