

11-4143

Lamp, Acquity® PDA/TUV 2489/2998 Performance Maintenance Kit
(2000 hr)

Comparable to: Waters® 201000281

Old: 201000186



Technical Data Sheet

1.0 Description

This lamp is designed to be compatible with Waters Acquity, Acquity UPLC® PDA, Acquity eLambda PDA, Acquity UPLC TUV, 2489 Dual Wavelength UV and 2998 PDA UHPLC detectors. It is comparable to Waters part number 201000281 and replaces old part number 201000186.



2.0 Specifications

2.1 Operating Specifications

Aperture Diameter: 0.5mm

Lifetime: 2000 hours

2.2 Materials

Socket Contacts: Pre-Tinned Brass

Connector Plug: Nylon, Natural Color

Lamp Envelope: UV Glass

3.0 Replacement Frequency

It is recommended that the lamp be replaced if it will not ignite, the noise or drift exceeds specifications, or if the lamp energy is below 50% of original intensity, as recorded during the initial installation.

4.0 Installation Information

Sciencix parts are designed to be compatible and interchangeable with OEM parts. Please see instrument service manual for proper removal and installation procedure.

5.0 Warranty

We view your business with us as a partnership based on mutual trust.

We extend a Lifetime Warranty against any manufacturing defects on all Sciencix HPLC repair parts. If a defect is identified, please contact us at 800.682.6480 or by email at sales@sciencix.com to report the issue. We will assist you with a resolution in a timely fashion.